








Telecoil Enabled Accessories

Accessory	Products	To purchase	General information
<u>Silhouettes</u>	Several brands / styles available	Available from a variety of businesses that carry products for individuals with hearing loss	Silhouettes can be used with cellular & cordless phones or with audio players. Products designed for phones have a 2.5mm plug and those for audio devices have a larger 3.5mm plug. Place earpiece next to processor and switch to T or MT (telecoil) setting. Use MT to hear your own voice. T can be used in noisy environments. Insert plug into headset jack. Single or bilateral models available.
Hatis®	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Mach 1</p>  </div> <div style="text-align: center;"> <p>Lite</p>  </div> </div>	www.cochlear.com www.harc.com www.soundbytes.com www.hatis.com	A light-weight, wafer-thin earpiece that fits comfortably and discreetly behind the ear. Plugs into hands-free 2.5mm jack on most cell phones. In-line microphone with advanced noise-canceling technology provides the highest level of voice transmission available.
NoiZfree™		www.harc.com www.harriscomm.com www.hear.com www.soundclarity.com	Durable for hard and intense use, and water resistant to sweat and rain, NoiZfree is a lightweight silhouette for telecoil (t-coil) users. Spiral cable for maximum comfort and durability.
Phonic Ear® Silhouette		www.adcohearing.com www.harc.com www.harriscomm.com	The silhouette style earpiece is placed over the ear, next to the processor to create the induction connection. Generally, the larger the surface area of the silhouette, the stronger the signal will be.
T-Links		www.soundclarity.com www.hearinglosshelp.com	Small and lightweight - doesn't take up much space behind your ears.
<u>NECKLOOPS</u> Clear Sounds® CLA7 Cellular Neckloop		www.hitec.com www.soundbytes.com www.harc.com www.soundclarity.com	Neckloops work with cellular, corded and cordless phones that have a 2.5mm headset jack. CLA7 includes adapter for use with a 3.5mm audio jack. Features up to 30+dB of amplification, 40 inch cord, powered with 2 standard AAA batteries.
Neckloop for Nokia Cell Phones		www.soundbytes.com www.harriscomm.com www.soundclarity.com	These neckloops are specially designed to fit the headset jacks of many Nokia cell phones. Use it for clear, handsfree conversations.



Compatible Cell Phones

Handsets that receive a compatibility rating of M3 or M4 have met (M3) or surpassed (M4) the ANSI compatibility standard for hearing devices as adopted by the Federal Communications Commission (FCC). The higher the M-rating the handset has the lower the radio frequency emissions level and higher signal quality the handset will have. If there is no M-rating, the handset does not meet the ANSI standard. The handset's M-rating will assist customers in finding a handset that will work best for them. The M rating evaluated phones with the hearing device in microphone mode.

As of September 15, 2006, several cellular providers have included at least two handsets that meet the ANSI Telecoil standard. Handsets that receive a telecoil rating of a T3 or T4 have met (T3) or surpassed (T4) the required standard as adopted by the FCC. Handsets below were those available in the local area. Information about compatibility with hearing devices (HAC) can be found on the cellular providers websites or in their retail stores. Check the details under each handset for information about the HAC rating. We recommend that you test all handsets in the stores prior to buying. Please remember that everyone's hearing loss is different and what works for one person may not work for another.

Cellular Provider	M3 / M4 Rated		T3 / T4 Rated		Informal User Testing T-Coil Compatible	Signal Technology
Verizon Wireless	LG VX9800 "the V" LG VX8300 Motorola Razr V3M Motorola V325 Samsung SCH a930 Samsung SCH a990	M3 M4 M4 M3 M3 M4	LG VX8300 Motorola RZR V3m Samsung SCHa990	T4 T4 T4	Samsung SCHa 950 Samsung SCHa 970 VZW XV6700 LG Chocolate Motorola Q	CDMA
Sprint / Nextel	Sanyo SCP-3100 Sanyo SCP-2400 Motorola C290 Samsung A640 LG PM225 LG Sprint Fusic	M3 M3 M3 M3 M3 M4	Sanyo SCP-3100 Sanyo SCP-2400 LG Sprint Fusic	T3 T3 T3	Sprint handsets (CDMA) are more compatible than Nextel with two way radio	CDMA / iDEN / GSM
Cingular / AT&T	LG C2000 LG CG300 Motorola V3i Samsung ZX20	M3 M3 M3 M3	LG C2000 Motorola V3i	T3 T3	Pantech C300 Nokia 6102i Samsung D807	GSM
T-Mobile *(phones listed as compatible – Rating not available)	Samsung T209* Samsung T809* Nokia 3650*	? ? ?			Samsung x495 Motorola V195	GSM

Bluetooth® Options

Product	Bluetooth Access	Works with
 Phonak MicroLink	Phonak SmartLink	Freedom BTE – MicroLink Freedom
“	“	Freedom Body-Worn & MicroLink MLXs
“	“	ESPrIt 3G – MicroLink MLXs & Adapter
 Starkey ELI	ELI Neckloop	Freedom or ESPrIt 3G in Telecoil Mode
“	ELI with MicroLink Adapter	ESPrIt 3G
Motorola HS850 Bluetooth Headset	Place headset next to processor in Telecoil Mode	Freedom BTE, Mini or Body-worn ESPrIt 3G



SmartLink SX



Starkey ELI



The gateway to communication

